



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 72F, SC/APC, 0 splitters, die. LT, 96F stubs, 100 ft, 12F

## Product Classification

<b>Product Type</b>	Fiber distribution hub
<b>Regional Availability</b>	North America
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Distribution Ports, quantity</b>	144
<b>Splitter Slots, quantity</b>	9
<b>Cable Type</b>	Dielectric - Loose Tube
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	1
<b>Fibers per Distribution Cable, quantity</b>	96
<b>Fibers per Feeder Cable, quantity</b>	12
<b>Interface Feature, input</b>	APC
<b>Interface, input</b>	SC
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Pallet

## Dimensions

<b>Enclosure Size</b>	Extra small
<b>Cable Length</b>	30.48 m   100.00 ft
<b>Depth</b>	356.00 mm   14.02 in
<b>Height</b>	762.00 mm   30.00 in
<b>Width</b>	533.00 mm   20.98 in

## Mechanical Specifications

<b>Mount Type</b>	Pole
<b>Access</b>	Front
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

**Environmental Space**

Aerial

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

