



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 144F, SC/APC, (2) 32-splitter module, die. LT, 100 ft, 12F

Product Classification

Product Type	Fiber distribution hub
Regional Availability	North America
Product Series	FDH 3000

General Specifications

Distribution Ports, quantity	144
Splitter Slots, quantity	9
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	12
Interface Feature, input	APC
Interface, input	SC
Package, quantity	1
Packaging Type	Pallet
Split Ratio	Symmetrical
Splitter Type	1 x 32
Splitter, quantity	2

Dimensions

Enclosure Size	Extra small
Cable Length	30.48 m 100.00 ft
Depth	356.00 mm 14.02 in
Height	762.00 mm 30.00 in
Width	533.00 mm 20.98 in

Mechanical Specifications

Mount Type	Pole
-------------------	------

Access	Front
Finish	Powder coated
Material Type	Steel

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

