



## 7-16 DIN Female High Power Termination Load, 70–2700 MHz

### **OBSOLETE**

This product was discontinued on: **March 31, 2012**

### **Replaced By**

7651924-01

7-16 DIN Female High Power Termination Load, 70–2700 MHz

## Product Classification

**Product Type** Termination load

## General Specifications

**Device Type** Termination Load

**Interface** 7-16 DIN Female

**Color** Silver

## Electrical Specifications

**Operating Frequency Band** 70 – 2700 MHz

**Average Power, maximum** 200 W

**Impedance** 50 ohm

**Return Loss, minimum** 20.0 dB

**VSWR** 1.25

## Environmental Specifications

**Ingress Protection Test Method** IEC 60529:2001, IP30

**Operating Temperature** -33 °C to +85 °C (-27.4 °F to +185 °F)

## Packed Dimensions

**Height** 242.0 mm | 9.5 in

**Length** 130.0 mm | 5.1 in

**Width** 165.0 mm | 6.5 in

**Shipping Weight** 370.00 g | 0.82 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

