

# T-2-NM

Termination Load, 0–3000 MHz



**This product will be discontinued on: December 31, 2019**

**Replaced By**

T-2-UW-NM                      Termination Load, 0–6000 MHz

## Product Classification

**Product Type**                      Termination load

## General Specifications

**Device Type**                      Termination Load

**Interface**                          N Male

**Color**                                Black

## Electrical Specifications

**Operating Frequency Band**      0 – 3000 MHz

**Average Power, maximum**      2 W

**Impedance**                         50 ohm

**Return Loss, minimum**            23.0 dB

**VSWR**                                1.15

## Mechanical Specifications

**Inner Contact Plating**             Silver

**Outer Contact Plating**             Trimetal

## Environmental Specifications

**Application**                         Indoor/Outdoor

**Ingress Protection Test Method** IEC 60529:2001, IP65

**Operating Temperature**          -35 °C to +50 °C (-31 °F to +122 °F)

**Relative Humidity**                 Up to 100%

# T-2-NM

---

## Dimensions

<b>Diameter, maximum</b>	20.00 mm   0.79 in
<b>Length</b>	40.50 mm   1.59 in
<b>Net Weight</b>	45.00 g   0.10 lb

## Packed Dimensions

<b>Height</b>	68.0 mm   2.7 in
<b>Length</b>	58.0 mm   2.3 in
<b>Width</b>	53.0 mm   2.1 in
<b>Shipping Weight</b>	65.00 g   0.14 lb
<b>Volume</b>	209.0 mm <sup>3</sup>

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

