

T-25-NM

Termination Load, 0–3000 MHz



This product will be discontinued on: December 31, 2019

Replaced By

T-25-UW-NM Termination Load, 0–6000 MHz

Product Classification

Product Type Termination load

General Specifications

Device Type Termination Load
Interface N Male
Color Black

Electrical Specifications

Operating Frequency Band 0 – 3000 MHz
Average Power, maximum 25 W
Impedance 50 ohm
Return Loss, minimum 23.0 dB
VSWR 1.15

Mechanical Specifications

Inner Contact Plating Silver
Outer Contact Plating Trimetal

Environmental Specifications

Application Indoor/Outdoor
Ingress Protection Test Method IEC 60529:2001, IP65
Operating Temperature -35 °C to +50 °C (-31 °F to +122 °F)

T-25-NM

Relative Humidity Up to 100%

Dimensions

Diameter, maximum 35.00 mm | 1.38 in
Length 81.50 mm | 3.21 in
Net Weight 165.00 g | 0.36 lb

Packed Dimensions

Height 98.0 mm | 3.9 in
Length 58.0 mm | 2.3 in
Width 53.0 mm | 2.1 in
Shipping Weight 195.00 g | 0.43 lb
Volume 302.0 mm³

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

