

LazrSPEED® 150 ST to SC, InstaPATCH® 360 Ruggedized Fanout Cable, 36-Fiber, Plenum

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360 LazrSPEED®
Product Type	Fiber fanout cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM2, bend insensitive
Total Fibers, quantity	36
Fibers per Subunit, quantity	12
Furcation Color	Aqua

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	3 m 8 ft
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Interface, connector A	ST/UPC
Interface, connector B	SC/UPC
Color, connector A	Black
Color, connector B	Beige
Construction Type	InstaPATCH® 360 ruggedized fanout, indoor
Cord Configurator	Yes

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
--	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

P-036-MP-5M-F12 (Product Component—not orderable) — LazrSPEED® Plenum MPO Trunk Cable, 36 fiber multi-unit with 12 fiber subunits

- CS-5M-MP (Product Component—not orderable) — LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber

700004328 | MFC-STU — Pre-Radiused ST II Connector, multimode

460125750 (Product Component—not orderable) — LazrSPEED® Pre-Radiused SC Connector for 1.6 mm Fiber Cordage, Duplex, multimode