

SVFAM10



HomeConnect® Inline Attenuator, F-m/F-f, 10 dB



Product Classification

Brand	HomeConnect®
Product Type	Coax attenuator

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	CE EN 60728-4 SCTE

Electrical Specifications

Operating Frequency Band	0 – 1002 MHz
Insertion Loss	10.00 dB
Frequency Response	±0.25 dB
Return Loss, input, minimum	25 dB
Return Loss, output, minimum	25 dB

General Specifications

Device Type	Attenuator
Application	Reduces RF signal levels by a specific value

Dimensions

Contact Pin Diameter	0.813 mm 0.032 in
Contact Pin Diameter Tolerance	±0.002 in

Mechanical Specifications

Material Type	Brass
Plating	Nickel

Packed Dimensions

Carton Quantity	2000
Height	241.30 mm 9.50 in

SVFAM10

Length	342.90 mm 13.50 in
Width	241.30 mm 9.50 in
Shipping Weight	25.40 kg 56.00 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

