



Uniprise Category 5e U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, White Jacket (Megapack of 100)

## **OBSOLETE**

**This product was discontinued on: March 31, 2017**

### **Replaced By**

CO155D2-08

CO5E-U-CM-WH

Category 5e U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, White Jacket

## Product Classification

<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	Twisted pair patch cord
<b>Regional Availability</b>	North America

## Dimensions

<b>Cord Length, maximum</b>	2 m   7 ft
<b>Cord Length, minimum</b>	1 ft   1 m

## Electrical Specifications

<b>ANSI/TIA Category</b>	5e
<b>dc Resistance, maximum</b>	0.30 ohm
<b>Safety Voltage Rating</b>	300 V

## Environmental Specifications

<b>Environmental Space</b>	Non-plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cETL   ETL

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Interface, connector A</b>	RJ45 plug
<b>Interface, connector B</b>	RJ45 plug
<b>Jacket Color</b>	White
<b>Interface Feature, connector A</b>	Standard
<b>Interface Feature, connector B</b>	Standard
<b>Package Quantity</b>	100

Pairs, quantity 4

## Mechanical Specifications

**Conductor Type** Stranded  
**Contact Plating Material** Precious metals  
**Material Type** Copper alloy | Polycarbonate  
**Plug Insertion Life, minimum** 750 times  
**Plug Retention Force, minimum** 133 N | 30 lbf  
**Wiring** T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015      **Classification** Designed, manufactured and/or distributed under this quality management system



## Included Products

CC4660044/BU | CC5ECM WHT 4/24 SR U/UTP RL BULK (Product Component—not orderable) — CC5ECM Category 5e U/UTP Cable, non-plenum, white jacket, 4 pair count, bulk length, reel