



OCC1A Wideband Splitter, singlemode, 1x2, 60/40 ratio, SC/APC, 2.0 mm cable, heavy duty housing

Product Classification

Product Type	Splitter component
Product Series	OCC1A
Regional Availability	North America

General Specifications

Distribution Type	1 x 2 splitter
Interface, input	SC
Interface, output	SC
Split Ratio	60/40
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Splitting
Interface Feature, input	APC
Interface Feature, output	APC
Package, quantity	1
Splitter, quantity	1
Technology Type	Fused biconic tapered

Dimensions

Pigtail Diameter	2.00 mm 0.08 in
Pigtail length, input	1.50 m 4.92 ft
Pigtail length, output	1.50 m 4.92 ft

Mechanical Specifications

Device Type	Component, tubular
--------------------	--------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

