

OCC1A Wideband Splitter, singlemode, 1x2, 85/15 ratio, 0.250 mm cable, light duty housing



Product Classification

Product Type	Splitter component
Product Series	OCC1A
Regional Availability	North America

General Specifications

Distribution Type	1 x 2 splitter
Interface, input	Stub tail
Interface, output	Stub tail
Split Ratio	85/15
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Splitting
Package, quantity	1
Splitter, quantity	1
Technology Type	Fused biconic tapered

Dimensions

Pigtail Diameter	0.25 mm 0.01 in
Pigtail length, input	2.50 m 8.20 ft
Pigtail length, output	2.50 m 8.20 ft

Mechanical Specifications

Device Type	Component, tubular
--------------------	--------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

