

OCC1A Wideband Splitter, singlemode, 1x2, 55/45 ratio, 0.250 mm cable, light duty housing



## Product Classification

<b>Product Type</b>	Splitter component
<b>Product Series</b>	OCC1A
<b>Regional Availability</b>	North America

## General Specifications

<b>Distribution Type</b>	1 x 2 splitter
<b>Interface, input</b>	Stub tail
<b>Interface, output</b>	Stub tail
<b>Split Ratio</b>	55/45
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Splitting
<b>Package, quantity</b>	1
<b>Splitter, quantity</b>	1
<b>Technology Type</b>	Fused biconic tapered

## Dimensions

<b>Pigtail Diameter</b>	0.25 mm   0.01 in
<b>Pigtail length, input</b>	2.50 m   8.20 ft
<b>Pigtail length, output</b>	2.50 m   8.20 ft

## Mechanical Specifications

<b>Device Type</b>	Component, tubular
--------------------	--------------------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

