



OCC1C CWDM, double mux/demux, 1511 nm starting wavelength, 0.9 mm cable, field installable

Product Classification

Product Type	CWDM component
Product Series	OCC1C
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Distribution Type	2-channel CWDM
Interface, input	Stub tail
Interface, output	Stub tail
Application	For use in FOSC closures
Circuits, quantity	2
Functionality	Multiplexing
Multiplexers, quantity	2
Package, quantity	1
Technology Type	Thin film filter (TFF)

Dimensions

Pigtail Diameter	0.90 mm 0.04 in
Pigtail length, input	2.50 m 8.20 ft
Pigtail length, output	2.50 m 8.20 ft

Mechanical Specifications

Device Type	Component, rectangular
--------------------	------------------------

Optical Specifications

Starting Wavelength	1511.00 nm
----------------------------	------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

