



OCC10 Wideband Splitter, low loss planar, singlemode, 1x8, symmetrical ratio, 0,250 mm cable, light duty housing

Product Classification

Product Type	Splitter component
Product Series	OCC10
Regional Availability	North America

General Specifications

Distribution Type	1 x 8 splitter
Interface, input	Stub tail
Interface, output	Stub tail
Split Ratio	Symmetrical
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Splitting
Package, quantity	1
Splitter, quantity	1
Technology Type	Planar lightwave circuit (PLC)

Dimensions

Pigtail Diameter	0.25 mm 0.01 in
Pigtail length, input	2.50 m 8.20 ft
Pigtail length, output	2.50 m 8.20 ft

Mechanical Specifications

Device Type	Component, rectangular
--------------------	------------------------

Environmental Specifications

Qualification Standard	Telcordia GR-1209-CORE Telcordia GR-1221-CORE
-------------------------------	---

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

