



OCC1P Wideband Splitter, planar, singlemode, 1x16, symmetrical split ratio, 0,9 mm cable, medium duty housing

Product Classification

Product Type	Splitter component
Product Series	OCC1P
Regional Availability	EMEA Latin America North America

General Specifications

Distribution Type	1 x 16 splitter
Interface, input	Stub tail
Interface, output	Stub tail
Split Ratio	Symmetrical
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Splitting
Package, quantity	1
Splitter, quantity	1
Technology Type	Planar lightwave circuit (PLC)

Dimensions

Pigtail Diameter	0.90 mm 0.04 in
Pigtail length, input	2.50 m 8.20 ft
Pigtail length, output	2.50 m 8.20 ft

Mechanical Specifications

Device Type	Component, rectangular
--------------------	------------------------

Environmental Specifications

Qualification Standard	Telcordia GR-1209-CORE Telcordia GR-1221-CORE
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

