



OCC1P Wideband Splitter, planar, singlemode, 1x4, symmetrical split ratio, 0.250 mm/ribbon cable, field installable

Product Classification

Product Type	Splitter component
Product Series	OCC1P
Regional Availability	EMEA Latin America North America

General Specifications

Distribution Type	1 x 4 splitter
Interface, input	Stub tail
Interface, output	Stub tail
Split Ratio	Symmetrical
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Splitting
Package, quantity	1
Splitter, quantity	1
Technology Type	Planar lightwave circuit (PLC)

Dimensions

Pigtail Diameter	0.25 mm 0.01 in
Pigtail length, input	2.50 m 8.20 ft
Pigtail length, output	2.50 m 8.20 ft

Mechanical Specifications

Device Type	Component, rectangular
--------------------	------------------------

Environmental Specifications

Qualification Standard	Telcordia GR-1209-CORE Telcordia GR-1221-CORE
-------------------------------	---

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

