



OCC1P Wideband Splitter, planar, singlemode, 2x32, symmetrical split ratio, LC/APC, 0.9 mm cable, medium duty housing

Product Classification

| | |
|------------------------------|--------------------------------------|
| Product Type | Splitter component |
| Product Series | OCC1P |
| Regional Availability | EMEA Latin America North America |

General Specifications

| | |
|----------------------------------|--------------------------------|
| Distribution Type | 2 x 32 splitter |
| Interface, input | LC |
| Interface, output | LC |
| Split Ratio | Symmetrical |
| Application | For use in FOSC closures |
| Circuits, quantity | 1 |
| Functionality | Splitting |
| Interface Feature, input | APC |
| Interface Feature, output | APC |
| Package, quantity | 1 |
| Splitter, quantity | 1 |
| Technology Type | Planar lightwave circuit (PLC) |

Dimensions

| | |
|-------------------------------|-------------------|
| Pigtail Diameter | 0.90 mm 0.04 in |
| Pigtail length, input | 1.50 m 4.92 ft |
| Pigtail length, output | 1.50 m 4.92 ft |

Mechanical Specifications

| | |
|--------------------|------------------------|
| Device Type | Component, rectangular |
|--------------------|------------------------|

Environmental Specifications

| | |
|-------------------------------|---|
| Qualification Standard | Telcordia GR-1209-CORE Telcordia GR-1221-CORE |
|-------------------------------|---|

Regulatory Compliance/Certifications

| | |
|---------------|-----------------|
| Agency | RoHS 2011/65/EU |
|---------------|-----------------|

| | |
|-----------------------|-----------|
| Classification | Compliant |
|-----------------------|-----------|

