



FOSC™ D-TRAY-72 type, DWDM, 12 channels, demux, 1561.42 nm starting wavelength, skipped channel spacing, SC/APC ports

## Product Classification

<b>Product Type</b>	DWDM splice tray
<b>Product Series</b>	FOSC-OC
<b>Product Brand</b>	FOSC™
<b>Regional Availability</b>	North America

## General Specifications

<b>Distribution Type</b>	12-channel DWDM
<b>Interface, input</b>	Stub tail
<b>Interface, output</b>	SC
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Demultiplexing
<b>Interface Feature, output</b>	APC
<b>Multiplexers, quantity</b>	1
<b>Package, quantity</b>	1
<b>Port Type, optional</b>	Tx and Rx test fibers   Upgrade port

## Dimensions

<b>Depth</b>	10.67 mm   0.42 in
<b>Height</b>	375.92 mm   14.80 in
<b>Pigtail Diameter</b>	0.25 mm   0.01 in
<b>Width</b>	152.40 mm   6.00 in

## Mechanical Specifications

<b>Device Type</b>	FOSC splice tray
--------------------	------------------

## Optical Specifications

<b>Starting Wavelength</b>	1561.42 nm
<b>Channel Spacing</b>	Skipped channels

## Regulatory Compliance/Certifications

**Agency**

**Classification**

RoHS 2011/65/EU

Compliant

