



FOSC™ A-TRAY-24 type, DWDM, 4 channels + upgrade port, demux, 1561.42 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Product Type	DWDM splice tray
Product Series	FOSC-OC
Product Brand	FOSC™
Regional Availability	North America

General Specifications

Distribution Type	4-channel DWDM
Interface, input	Stub tail
Interface, output	Stub tail
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Demultiplexing
Multiplexers, quantity	1
Package, quantity	1
Port Type, optional	Tx and Rx test fibers Upgrade port

Dimensions

Depth	10.67 mm 0.42 in
Height	233.68 mm 9.20 in
Pigtail Diameter	0.90 mm 0.04 in

Mechanical Specifications

Device Type	FOSC splice tray
--------------------	------------------

Optical Specifications

Starting Wavelength	1561.42 nm
Channel Spacing	100 GHz

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

