



FOSC™ A-TRAY-24 type, DWDM, 8 channels + upgrade port, demux, 1561.42 nm starting wavelength, 100 GHz channel spacing

Product Classification

Product Type	DWDM splice tray
Product Series	FOSC-OC
Product Brand	FOSC™
Regional Availability	North America

General Specifications

Distribution Type	8-channel DWDM
Interface, input	Stub tail
Interface, output	Stub tail
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Demultiplexing
Multiplexers, quantity	1
Package, quantity	1
Port Type, optional	Upgrade port

Dimensions

Depth	10.67 mm 0.42 in
Height	9.20 mm 0.36 in
Pigtail Diameter	0.25 mm 0.01 in

Mechanical Specifications

Device Type	FOSC splice tray
--------------------	------------------

Optical Specifications

Starting Wavelength	1561.42 nm
Channel Spacing	100 GHz

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

