



FOSC™ A-TRAY-24 type, DWDM, 16 channels, demux, 1554.94 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Product Type	DWDM splice tray
Product Series	FOSC-OC
Product Brand	FOSC™
Regional Availability	North America

General Specifications

Distribution Type	16-channel DWDM
Interface, input	Stub tail
Interface, output	Stub tail
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Demultiplexing
Multiplexers, quantity	1
Package, quantity	1
Port Type, optional	Upgrade port

Dimensions

Depth	10.67 mm 0.42 in
Height	233.68 mm 9.20 in
Pigtail Diameter	0.25 mm 0.01 in
Width	99.06 mm 3.90 in

Mechanical Specifications

Device Type	FOSC splice tray
--------------------	------------------

Optical Specifications

Starting Wavelength	1554.94 nm
Channel Spacing	100 GHz

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

