



OCM5 Fiber Optic Splitter Module, Planar, two 1x16 Splitters, singlemode, SC/APC, symmetrical split ratio, 3.0 m pigtailed

Product Classification

Product Type	Splitter module
Product Series	OCM5
Regional Availability	EMEA

General Specifications

Distribution Type	1 x 16 splitter
Interface, input	SC
Interface, output	SC
Split Ratio	Symmetrical
Application	For use with FIST cabinets
Circuits, quantity	2
Functionality	Splitting
Interface Feature, input	APC
Interface Feature, output	APC
Package, quantity	1
Packaging Type	Box Carton
Splitter, quantity	2
Technology Type	Planar lightwave circuit (PLC)

Dimensions

Depth	142.00 mm 5.59 in
Height	154.00 mm 6.06 in
Pigtail length, input	3.00 m 9.84 ft
Pigtail length, output	3.00 m 9.84 ft
Width	16.00 mm 0.63 in

Mechanical Specifications

Device Type	Standard VAM
Access	Front

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

