



OCM6 Fiber Optic Splitter Module, FBT, eight 2x2 Splitters, singlemode, LC/APC, symmetrical split ratio, butt style, 1.6 m pigtails

Product Classification

Product Type	Splitter module
Product Series	OCM6
Regional Availability	EMEA

General Specifications

Distribution Type	2 x 2 splitter
Interface, input	LC
Interface, output	LC
Split Ratio	Symmetrical
Application	For use with BUDI wall boxes
Circuits, quantity	8
Functionality	Splitting
Interface Feature, input	APC
Interface Feature, output	APC
Package, quantity	1
Splitter, quantity	8
Technology Type	Fused biconic tapered

Dimensions

Depth	16.50 mm 0.65 in
Height	130.00 mm 5.12 in
Pigtail Diameter	1.80 mm 0.07 in
Pigtail length, input	1.60 m 5.25 ft
Pigtail length, output	1.60 m 5.25 ft
Width	49.80 mm 1.96 in

Mechanical Specifications

Device Type	Standard VAM
--------------------	--------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

