



OCM6 Fiber Optic Splitter Module, Planar, one 1x16 Splitter, singlemode, LC/APC, symmetrical split ratio, butt style, 61 cm pigtails

Product Classification

Product Type	Splitter module
Product Series	OCM6
Regional Availability	EMEA

General Specifications

Distribution Type	1 x 16 splitter
Interface, input	LC
Interface, output	LC
Split Ratio	Symmetrical
Application	For use with BUDI wall boxes
Circuits, quantity	1
Functionality	Splitting
Interface Feature, input	APC
Interface Feature, output	APC
Package, quantity	1
Splitter, quantity	1
Technology Type	Planar lightwave circuit (PLC)

Dimensions

Depth	16.50 mm 0.65 in
Height	130.00 mm 5.12 in
Pigtail Diameter	1.80 mm 0.07 in
Pigtail length, input	610.00 mm 24.02 in
Pigtail length, output	610.00 mm 24.02 in
Width	49.80 mm 1.96 in

Mechanical Specifications

Device Type	Standard VAM
--------------------	--------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

