



OCM1 LGX Fiber Optic Module, CWDM, Mux/Demux, LC/APC, 2 channels, starting wavelength 1510 nm

Product Classification

Product Type	CWDM module
Product Series	LSX OCM1
Regional Availability	North America

General Specifications

Distribution Type	2-channel CWDM
Interface, input	LC
Interface, output	LC
Application	For use with LGX panels
Circuits, quantity	1
Functionality	Demultiplexing Multiplexing
Interface Feature, input	APC
Interface Feature, output	APC
Multiplexers, quantity	1
Package, quantity	1
Packaging Type	Box Carton
Technology Type	Thin film filter (TFF)

Dimensions

Depth	127.00 mm 5.00 in
Height	129.54 mm 5.10 in
Width	27.94 mm 1.10 in

Mechanical Specifications

Device Type	Standard VAM
--------------------	--------------

Optical Specifications

Starting Wavelength	1510.00 nm
----------------------------	------------

Channel Spacing 20 nm

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

