



OCM1 LGX Fiber Optic Module, DWDM, Mux, SC/UPC, 8 channels, upgrade port, starting wavelength 1553.33 nm

Product Classification

Product Type	DWDM module
Product Series	LSX OCM1
Regional Availability	North America

General Specifications

Distribution Type	8-channel DWDM
Interface, input	SC
Interface, output	SC
Application	For use with LGX panels
Circuits, quantity	1
Functionality	Multiplexing
Interface Feature, input	Standard
Interface Feature, output	Standard
Multiplexers, quantity	1
Package, quantity	1
Packaging Type	Box Carton
Port Type, optional	Upgrade port

Dimensions

Depth	127.00 mm 5.00 in
Height	129.54 mm 5.10 in
Width	58.42 mm 2.30 in

Mechanical Specifications

Device Type	Standard VAM
--------------------	--------------

Optical Specifications

Starting Wavelength	1553.33 nm
----------------------------	------------

Channel Spacing 100 GHz

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

