



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode

Product Classification

Product Type Optical module

General Specifications

Input Connector Interface LC

Note Detailed Product Specifications are available. Please contact your local CommScope representative.

Optical Interface

Fiber Type 9/125 μm , singlemode

Wavelength 1310.0 nm

Environmental Specifications

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Dimensions

Depth 57.00 mm | 2.24 in

Height 12.00 mm | 0.47 in

Width 14.00 mm | 0.55 in