



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode

## Product Classification

**Product Type** Optical module

## General Specifications

**Input Connector Interface** LC

**Note** Detailed Product Specifications are available. Please contact your local CommScope representative.

## Optical Interface

**Fiber Type** 9/125  $\mu\text{m}$ , singlemode

**Wavelength** 1390.0 nm

## Environmental Specifications

**Operating Temperature** 0 °C to +70 °C (+32 °F to +158 °F)

## Dimensions

**Depth** 57.00 mm | 2.24 in

**Height** 12.00 mm | 0.47 in

**Width** 14.00 mm | 0.55 in