



Angle Adapter, compact 3/8 in tapped hole

Product Classification

Product Type Adapter

Dimensions

Inside Length 15.88 mm | 0.63 in
Inside Width 15.88 mm | 0.63 in
Outside Length 46.99 mm | 1.85 in
Outside Width 38.10 mm | 1.50 in

General Specifications

Adapter Type Angle adapter
Material Type Stainless steel
Ordering Note CommScope® standard product in Mexico, Central America, and South America
Package Quantity 10

Mechanical Specifications

Installation Torque, maximum 13.0 ft lb
Installation Torque, minimum 11.0 ft lb
Material Thickness 2.972 mm | 0.117 in
Maximum Loading Double stack, 1-5/8 in cable
Mounting 3/8 in tapped hole

Packed Dimensions

Height 14.0 cm | 5.5 in
Length 11.0 cm | 4.3 in
Shipping Weight 1.32 kg | 2.91 lb
Width 14.0 cm | 5.5 in

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

243684

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014

Compliant
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)

