



Stand-off Adapter, 3/8 in tapped hole

Product Classification

Brand	I-Line
Product Type	Adapter

Dimensions

Inside Length	60.33 mm 2.38 in
Inside Width	44.45 mm 1.75 in
Outside Length	38.10 mm 1.50 in
Outside Width	57.15 mm 2.25 in

General Specifications

Adapter Type	Stand-off adapter
Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Installation Torque, maximum	15.0 ft lb
Installation Torque, minimum	11.0 ft lb
Material Thickness	2.667 mm 0.105 in
Maximum Loading	Double stack, 1-5/8 in cable
Mounting	3/8 in tapped hole

Packed Dimensions

Height	17.0 cm 6.7 in
Length	10.0 cm 3.9 in
Shipping Weight	1.70 kg 3.75 lb
Width	13.0 cm 5.1 in