

31768A-M

Angle Adapter, standard, M10 tapped hole



Product Classification

Product Type Adapter

Dimensions

| | |
|-----------------------|--------------------|
| Inside Length | 22.23 mm 0.88 in |
| Inside Width | 22.23 mm 0.88 in |
| Outside Length | 44.96 mm 1.77 in |
| Outside Width | 49.81 mm 1.96 in |

General Specifications

| | |
|-------------------------|---------------------------------|
| Adapter Type | Angle adapter |
| Material Type | Stainless steel |
| Ordering Note | CommScope® non-standard product |
| Package Quantity | 10 |

Mechanical Specifications

| | |
|-------------------------------------|------------------------------|
| Installation Torque, maximum | 15.0 ft lb |
| Installation Torque, minimum | 11.0 ft lb |
| Material Thickness | 4.191 mm 0.165 in |
| Maximum Loading | Triple stack, 1-5/8 in cable |
| Mounting | M10 tapped hole |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 14.2 cm 5.6 in |
| Length | 10.2 cm 4.0 in |
| Shipping Weight | 2.33 kg 5.14 lb |
| Width | 14.2 cm 5.6 in |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

