

Angle Adapter, standard, 3/8 in tapped hole



Product Classification

Product Type Adapter

Dimensions

Inside Length	22.23 mm 0.88 in
Inside Width	22.23 mm 0.88 in
Outside Length	44.96 mm 1.77 in
Outside Width	49.81 mm 1.96 in

General Specifications

Adapter Type	Angle adapter
Material Type	Stainless steel
Ordering Note	CommScope® standard product in the United States and Canada
Package Quantity	10

Mechanical Specifications

Installation Torque, maximum	15.0 ft lb
Installation Torque, minimum	11.0 ft lb
Material Thickness	4.191 mm 0.165 in
Maximum Loading	Triple stack, 1-5/8 in cable
Mounting	3/8 in tapped hole

Packed Dimensions

Height	14.2 cm 5.6 in
Length	10.2 cm 4.0 in
Shipping Weight	2.33 kg 5.14 lb
Width	14.2 cm 5.6 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

