

1316MCLICK



Miniature Click-on Hanger for 13–16 mm cable - Hardware Sold Separately

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size	1/2 in 3/8 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	13.716 mm 0.540 in
Height	38.00 mm 1.50 in
Length	55.00 mm 2.17 in
Width	25.00 mm 0.98 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type	Click-on hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa CommScope® standard product in the United States and Canada
Package Quantity	10

Mechanical Specifications

Mounting	M8 through hole
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber

1316MCLICK

Vibration Survival =4 hours at resonant frequency
Environmental Strength Capability Double cable weight

Packed Dimensions

Height 44.7 cm | 17.6 in
Length 17.7 cm | 7.0 in
Shipping Weight 0.05 kg | 0.12 lb
Width 39.4 cm | 15.5 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power