



Universal Snap-in Hanger for 1/2 in corrugated, smoothwall, and braided coaxial cable

### **OBSOLETE**

#### **Replaced By**

SSH-12

SnapStak® Hanger for 1/2 in coaxial cable

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	1/2 in
<b>Compatible Diameter, maximum</b>	16.256 mm   0.640 in
<b>Compatible Diameter, minimum</b>	13.716 mm   0.540 in
<b>Height</b>	41.00 mm   1.61 in
<b>Length</b>	61.00 mm   2.40 in
<b>Width</b>	34.90 mm   1.37 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel

<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/4 in drilled cable ladder
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	17.0 cm   6.7 in
<b>Length</b>	10.0 cm   3.9 in
<b>Shipping Weight</b>	0.35 kg   0.78 lb
<b>Width</b>	13.0 cm   5.1 in