



Universal Snap-in Hanger for 7/8 in corrugated, smoothwall, and braided coaxial cable

Product Classification

Brand	I-Line
Product Type	Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	30.988 mm 1.220 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	41.00 mm 1.61 in
Length	71.00 mm 2.80 in
Width	37.00 mm 1.46 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Cables per Hanger	1
Color	Silver
Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation =500 hours in salt spray chamber

Mounting 3/4 in drilled cable ladder

Vibration Survival =4 hours at resonant frequency

Environmental Strength Capability Double cable weight

Packed Dimensions

Height 17.0 cm | 6.7 in

Length 10.0 cm | 3.9 in

Shipping Weight 0.44 kg | 0.96 lb

Width 13.0 cm | 5.1 in