



Universal Snap-in Hanger for 1-1/4 in corrugated, smoothwall, and braided coaxial cable

OBSOLETE

This product was discontinued on: **September 16, 2015**

Replaced By

SSH-114

SnapStak® Hanger for 1-1/4 in coaxial cable

Product Classification

Brand	I-Line
Product Type	Hanger kit

Dimensions

Nominal Size	1-1/4 in
Compatible Diameter, maximum	43.180 mm 1.700 in
Compatible Diameter, minimum	37.592 mm 1.480 in
Height	41.00 mm 1.61 in
Length	86.00 mm 3.39 in
Width	38.80 mm 1.53 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Cables per Hanger	1
Color	Silver

Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/4 in drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	17.0 cm 6.7 in
Length	10.0 cm 3.9 in
Shipping Weight	0.72 kg 1.58 lb
Width	13.0 cm 5.1 in