



Universal Snap-in Hanger for 2-1/4 in corrugated coaxial cable

**OBSOLETE**

This product was discontinued on: September 1, 2015

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	2-1/4 in
<b>Compatible Diameter, maximum</b>	59.944 mm   2.360 in
<b>Compatible Diameter, minimum</b>	58.166 mm   2.290 in
<b>Height</b>	41.00 mm   1.61 in
<b>Length</b>	104.00 mm   4.09 in
<b>Width</b>	44.50 mm   1.75 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Material Type</b>	Stainless steel

<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/4 in drilled cable ladder
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	30.4 cm   12.0 in
<b>Length</b>	6.3 cm   2.5 in
<b>Shipping Weight</b>	0.80 kg   1.76 lb
<b>Width</b>	27.9 cm   11.0 in