



Butterfly Hanger for 2-1/4 in corrugated coaxial cable

OBSOLETE

This product was discontinued on: **October 1, 2013**

Replaced By

42396A-4

Butterfly Hanger for 2-1/4 in coaxial cable and elliptical waveguide 37

Product Classification

Brand	I-Line
Product Type	Hanger kit

Dimensions

Nominal Size	2-1/4 in
Compatible Diameter, maximum	59.944 mm 2.360 in
Compatible Diameter, minimum	58.166 mm 2.290 in
Height	82.00 mm 3.23 in
Length	110.00 mm 4.33 in
Width	38.10 mm 1.50 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Standard butterfly hanger
Cables per Hanger	1

Color	Silver
Material Type	Stainless steel
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/8 in (M10) drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	33.0 cm 13.0 in
Length	6.0 cm 2.4 in
Shipping Weight	0.74 kg 1.64 lb
Width	22.0 cm 8.7 in