



Cushion Hanger Assembly for 7/8 in corrugated coaxial cable, one hole

OBSOLETE

Product Classification

| | |
|---------------------|------------|
| Brand | I-Line |
| Product Type | Hanger kit |

Dimensions

| | |
|-------------------------------------|----------------------|
| Nominal Size | 7/8 in |
| Compatible Diameter, maximum | 30.988 mm 1.220 in |
| Compatible Diameter, minimum | 26.670 mm 1.050 in |
| Height | 25.40 mm 1.00 in |
| Length | 96.00 mm 3.78 in |
| Width | 79.75 mm 3.14 in |

Electrical Specifications

| | |
|---------------------------|--------|
| DTF Effect | 0.1 dB |
| Return Loss Effect | 0.1 dB |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
|------------------------------|--------------------------------------|

General Specifications

| | |
|--------------------------|---------------------------------|
| Hanger Type | Cushion hanger |
| Cables per Hanger | 1 |
| Color | Black |
| Material Type | Engineered plastic |
| Ordering Note | CommScope® non-standard product |
| Package Quantity | 10 |

Mechanical Specifications

| | |
|----------------------------------------------------------|----------------------------------------------------|
| Corrosion Resistance, minimum with no degradation | ≥500 hours in salt spray chamber |
| Mounting | 3/8 in (M10) drilled cable ladder |
| UV Resistance, minimum with no degradation | ≥100 hours exposure in accelerated UV life chamber |
| Vibration Survival | ≥4 hours at resonant frequency |
| Environmental Strength Capability | Double cable weight |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 17.0 cm 6.7 in |
| Length | 10.0 cm 3.9 in |
| Shipping Weight | 0.44 kg 0.96 lb |
| Width | 13.0 cm 5.1 in |