



Cushion Hanger Assembly for 7/8 in corrugated coaxial cable, two holes

**OBSOLETE**

## Product Classification

<b>Brand</b>	I-Line
<b>Product Type</b>	Hanger kit

## Dimensions

<b>Nominal Size</b>	7/8 in
<b>Compatible Diameter, maximum</b>	30.988 mm   1.220 in
<b>Compatible Diameter, minimum</b>	26.670 mm   1.050 in
<b>Height</b>	25.40 mm   1.00 in
<b>Length</b>	96.00 mm   3.78 in
<b>Width</b>	79.75 mm   3.14 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Hanger Type</b>	Cushion hanger
<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Material Type</b>	Engineered plastic
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/8 in (M10) drilled cable ladder
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	17.0 cm   6.7 in
<b>Length</b>	10.0 cm   3.9 in
<b>Shipping Weight</b>	0.44 kg   0.96 lb
<b>Width</b>	13.0 cm   5.1 in