

Butterfly Hanger for 1-5/8 in coaxial cable



Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-5/8 in
Compatible Diameter, maximum 52.070 mm | 2.050 in
Compatible Diameter, minimum 48.260 mm | 1.900 in
Height 70.00 mm | 2.76 in
Length 88.90 mm | 3.50 in
Width 38.10 mm | 1.50 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Standard butterfly hanger
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Ordering Note CommScope® standard product in Mexico, Central America, and South America | CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

42396A-2

Mounting	3/8 in (M10) drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	25.4 cm 10.0 in
Length	17.7 cm 7.0 in
Shipping Weight	0.56 kg 1.24 lb
Width	39.4 cm 15.5 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

