

## Butterfly Hanger for 2-1/4 in coaxial cable and elliptical waveguide 37



## Product Classification

**Product Type** Hanger kit

## Dimensions

**Nominal Size** 2-1/4 in  
**Compatible Diameter, maximum** 59.944 mm | 2.360 in  
**Compatible Diameter, minimum** 58.166 mm | 2.290 in  
**Height** 82.00 mm | 3.23 in  
**Length** 110.00 mm | 4.33 in  
**Width** 38.10 mm | 1.50 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

**Hanger Type** Standard butterfly hanger  
**Cables per Hanger** 1  
**Color** Silver  
**Material Type** Stainless steel  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 10

## Mechanical Specifications

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber  
**Mounting** 3/8 in (M10) drilled cable ladder

# 42396A-4

---

**Vibration Survival** ≥4 hours at resonant frequency  
**Environmental Strength Capability** Double cable weight

## Packed Dimensions

**Height** 33.0 cm | 13.0 in  
**Length** 6.0 cm | 2.4 in  
**Shipping Weight** 0.74 kg | 1.64 lb  
**Width** 22.0 cm | 8.7 in

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system  
Below Maximum Concentration Value (MCV)

