



Butterfly Hanger for 1/2 in or 3/8 in coaxial cable and elliptical waveguide 180, 220, and 240

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1/2 in
Compatible Diameter, maximum 16.256 mm | 0.640 in
Compatible Diameter, minimum 10.414 mm | 0.410 in
Height 31.75 mm | 1.25 in
Length 40.64 mm | 1.60 in
Width 38.10 mm | 1.50 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Standard butterfly hanger
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Ordering Note CommScope® standard product in Mexico, Central America, and South America | CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber
Mounting 3/8 in (M10) drilled cable ladder
Vibration Survival ≥4 hours at resonant frequency

43211A

Environmental Strength Capability

Double cable weight

Packed Dimensions

Height	14.8 cm 5.8 in
Length	9.0 cm 3.5 in
Shipping Weight	0.34 kg 0.75 lb
Width	10.6 cm 4.2 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

