



Miniature Click-on Hanger for 9–12 mm cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1/4 in | 3/8 in
Compatible Diameter, maximum 11.989 mm | 0.472 in
Compatible Diameter, minimum 8.992 mm | 0.354 in
Height 38.00 mm | 1.50 in
Length 43.00 mm | 1.69 in
Width 20.00 mm | 0.79 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Click-on hanger
Cables per Hanger 2
Color Black
Material Type Engineered plastic
Maximum Stack Height 3
Ordering Note CommScope® standard product in Mexico, Central America, and South America
Package Quantity 10

Mechanical Specifications

Mounting M8 through hole
UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

912MCLICK

Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	15.2 cm 6.0 in
Length	2.5 cm 1.0 in
Shipping Weight	0.13 kg 0.29 lb
Width	20.3 cm 8.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power