



Weatherproofing Kit for Connectors and Splices, includes butyl rubber and PVC tape

## Product Classification

**Product Type** Weatherproofing tape

## Dimensions

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

## General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit** Four 1/2 in–7/8 in | Twelve 1/2 in–1/2 in | Twelve 1/2 in–7/8 in to device | Two 1/2 in–2-1/4 in

**Harmonized System (HS) Code** 854420 (Coaxial cable and other coaxial electric conductors)

**Includes** One roll of 2 in PVC tape | Six rolls of 2-1/2 in butyl rubber tape | Two rolls of 3/4 in PVC tape

**Material Type** Butyl rubber tape | PVC tape

**Ordering Note** CommScope® standard product (Global)

**Package Quantity** 1

## Mechanical Specifications

**UV Resistance Test Method** Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F | PVC tape test method UL 510, ASTM D1000

**UV Resistance, minimum with no degradation** =1000 hours

**Weather Resistance Test Method** 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

## Packed Dimensions

**Height** 19.6 cm | 7.7 in

**Length** 9.6 cm | 3.8 in

**Shipping Weight** 1.52 kg | 3.35 lb

**Width** 17.4 cm | 6.9 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# 221213

---

China RoHS SJ/T 11364-2014

Below Maximum Concentration Value (MCV)



## Included Products

42615-10 — Butyl Rubber Tape, 24 in

9905-41 — Black 3/4 in PVC Tape, 66 ft

9905-71 — Black 2 in PVC Tape, 20 ft