



Cold shrink Kit for 5/8 in to 1/4 in through 1/2 in connections

Product Classification

Product Type Cold shrink kit

Dimensions

Nominal Size 1/2 in | 1/4 in | 5/8 in
Cable Diameter for Seal, maximum 20.32 mm | 0.80 in
Cable Diameter for Seal, minimum 7.37 mm | 0.29 in
Inner Diameter 51.31 mm | 2.02 in
Length 254.00 mm | 10.00 in
Width 53.85 mm | 2.12 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit One 1/4 in–1/2 in to 5/8 in
Color Black
Includes One EPDM rubber tube | One sealing foam strip
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation =1000 hours
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 29.2 cm | 11.5 in
Length 7.8 cm | 3.1 in
Shipping Weight 0.16 kg | 0.35 lb
Width 7.8 cm | 3.1 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)

