



Cold shrink Kit for 1-5/8 in or 1-1/4 in to 1/4 in through 1/2 in connections

Product Classification

Product Type Cold shrink kit

Dimensions

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 3/8 in
Cable Diameter for Seal, maximum 30.48 mm | 1.20 in
Cable Diameter for Seal, minimum 7.37 mm | 0.29 in
Inner Diameter 69.85 mm | 2.75 in
Length 330.20 mm | 13.00 in
Width 72.39 mm | 2.85 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit One 1/4 in–1/2 in to 1-5/8 in or 1-1/4 in
Color Black
Includes One EPDM rubber tube | One sealing foam strip
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation =1000 hours
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 30.0 cm | 11.8 in
Length 8.0 cm | 3.1 in
Shipping Weight 0.34 kg | 0.74 lb
Width 8.0 cm | 3.1 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

