



Cold shrink Kit for 1/2 in through 7/8 in antenna and device 7/16 DIN connections

Product Classification

Product Type Cold shrink kit

Dimensions

Nominal Size 1/2 in | 7/8 in
Cable Diameter for Seal, maximum 21.34 mm | 0.84 in
Cable Diameter for Seal, minimum 16.00 mm | 0.63 in
Inner Diameter 52.98 mm | 2.09 in
Length 202.95 mm | 7.99 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit One 1/2 in–7/8 in
Color Black
Includes One EPDM rubber tube | One sealing foam strip
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation =1000 hours
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 25.5 cm | 10.0 in
Length 6.4 cm | 2.5 in
Shipping Weight 0.16 kg | 0.34 lb
Width 6.4 cm | 2.5 in

Regulatory Compliance/Certifications

Agency **Classification**

245174

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

