



Butyl Rubber Tape, 24 in

## Product Classification

**Product Type** Weatherproofing tape

## Dimensions

**Length** 609.60 mm | 24.00 in

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

**Width** 63.50 mm | 2.50 in

## General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit** One 1/2 in–2-1/4 in | One 1/2 in–7/8 in | One 1/2 in–7/8 in to device | Two 1/2 in–1/2 in

**Color** Black

**Material Type** Butyl rubber tape

**Ordering Note** CommScope® non-standard product

**Package Quantity** 1

## Mechanical Specifications

**UV Resistance Test Method** Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F

**UV Resistance, minimum with no degradation** =1000 hours

**Weather Resistance Test Method** 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

## Packed Dimensions

**Height** 6.4 cm | 2.5 in

**Length** 2.5 cm | 1.0 in

**Shipping Weight** 0.17 kg | 0.37 lb

**Width** 69.9 mm | 2.8 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

**Classification**

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

