



Black 3/4 in PVC Tape, 66 ft

Product Classification

Product Type Weatherproofing tape

Dimensions

Length 20.12 m | 66.00 ft
Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in
Width 19.05 mm | 0.75 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit Four 1/2 in–1/2 in | Four 1/2 in–7/8 in to device | One 1/2 in–2-1/4 in | Two 1/2 in–7/8 in
Color Black
Material Type PVC tape
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method PVC tape test method UL 510, ASTM D1000
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 6.2 cm | 2.4 in
Length 1.9 cm | 0.8 in
Shipping Weight 0.11 kg | 0.24 lb
Width 6.2 cm | 2.4 in

Regulatory Compliance/Certifications

Agency ISO 9001:2015
Classification Designed, manufactured and/or distributed under this quality management system

