



Black 2 in PVC Tape, 20 ft

Product Classification

Product Type Weatherproofing tape

Dimensions

Length 6.10 m | 20.00 ft

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

Width 50.80 mm | 2.00 in

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit Four 1/2 in–1/2 in | Four 1/2 in–7/8 in to device | One 1/2 in–2-1/4 in | Two 1/2 in–7/8 in

Color Black

Material Type PVC tape

Ordering Note CommScope® non-standard product

Package Quantity 1

Mechanical Specifications

UV Resistance Test Method PVC tape test method UL 510, ASTM D1000

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 6.4 cm | 2.5 in

Length 5.1 cm | 2.0 in

Shipping Weight 0.08 kg | 0.19 lb

Width 6.4 cm | 2.5 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

